



Mixing ratio	23-24 ml /100 gr
Mixing time by hand/Mixer	60" / 30"
Working time	6'
Final setting time (Vicat)	8'
Demoulding time	35'
Setting Expansion (2 h)	< 0.12%
Compression Strenght (1 h)	> 35 MPa

Type IV hard, thixotropic and characterized by a reduced setting expansion and excellent flow.

**PLUSROCK** allows a faithful copy of even the most minute details and is ideal for obtaining precision models for all types of work and for master models. Exceptional for the creation of masks and implantation templates for repositioning, where an elevated surface resistance is needed.

CODE	PACKAGING
<b>DGSS25 LY</b>	White paper bag kg 25
<b>DGS20 LY</b>	Rectangular plastic drum kg 20
<b>DGS25 LY</b>	Conic plastic drum kg 25

Standard color: **LY**= Light yellow

Color customization is available upon request.